



Technical Data

Phonak Naída B

Phonak Naída B-UP (B90/B70/B50/B30) (HE11)

WaterResistant compact UltraPower BTE, battery size 675 (for fitting range, product details and available options, please see Product Information or visit www.phonakpro.com).




Warning to hearing care professionals:
This hearing instrument has an output sound pressure level that can exceed 132 dB SPL. Special care should be taken when fitting this instrument as there is a risk of impairing the residual hearing of the user.


Ear simulator data

IEC 60118-0: 1994

Output sound pressure level




Acoustic gain



Frequency range	<100 Hz - 5100 Hz		
Total harmonic distortion	500 Hz	800 Hz	1600 Hz
	8%	3%	1.5%
Battery current	Quiescent	Working	
	1.1 mA	1.3 mA	
Equivalent input noise level	19 dB SPL		

Induction coil sensitivity




Using pure tone measurements with a digital hearing instrument can result in a wavy frequency response. This is an artifact resulting from the use of a narrowband input signal and does not affect the actual performance with naturally occurring broadband input signals.

2cm³ coupler data


ANSI/ASA S3.22-2014

IEC 60118-0: 2015

Output sound pressure level




Acoustic gain



Frequency range	<100 Hz - 4800 Hz		
Total harmonic distortion	500 Hz	800 Hz	1600 Hz
	5%	1%	1%
Battery current	2mA		
Equivalent input noise level	19 dB SPL		

Induction coil sensitivity



Absolute Hearing Solutions LLC

absolutehearing@att.net

750 Cross Pointe Road Suite F
Gahanna, Ohio 43230

Phone: 614-452-4280

Toll Free: 888-803-2139

Fax: 614-577-0481

www.absolutehearingsolutions.com

Call
Absolute Hearing Solutions
For Hearing Aid Details!
614-452-4280

www.absolutehearingsolutions.com

Call
Absolute Hearing Solutions
For Hearing Aid Details!
614-452-4280

www.absolutehearingsolutions.com



PHONAK

A Sonova brand